



STL Stellar 200 Fibre

ITU-T G.657.A2 Single Mode Optical Fibre

Product Description

STL Stellar 200 Fibre is the first to offer ITU-T G.657.A2 bend performance with a 9.1-micron standard mode field diameter, ensuring complete compatibility with existing networks. The induced loss of this fibre at the tightest bends is a factor of two lower than the ITU-T G.657.A2 standard, providing installation and operational efficiencies in high density networks. This low bend loss extends to the longer wavelengths required for future system upgrades. The 200um diameter of this fibre enables very high-density cables with small diameters which allow service providers to maximize the number of fibre s that can be installed in existing ducts or to minimize the size or even the need for new ducting and related infrastructure. Low bend loss and reduced diameter fibres allow operators to optimize their physical asset utilization and future proof their high-density networks.

Product Application

The need to install more fibre in less space has led to wider application of bend insensitive fibres and reduced diameter fibres. STL Stellar 200 Optical Fibre is suitable for use in high density networks where full backward compatibility with existing fibres is required.

Product Benefits

- Completely compatible with existing networks built with G.652.D and G.657.A1 fibres due to 9.1 micron standard mode field diameter.
- Provides installation and operational efficiencies and enables the use of compact closures and accessories due to low bend loss.
- Future system ready In that low bend loss extends to the longer wavelengths required for future system upgrades.
- Increases the number of fibres that can be installed in existing infrastructure by enabling close to double the number of fibres in the same cable diameter.
- Minimizes the space required in ducts and related infrastructure by enabling reduction in cable cross section area by about 30% for the same number of fibres.

Standard Compliance

STL routinely calibrates and recertifies process equipment and measurement benches against internationally traceable standards from NPL/NIST, and follow test methods compliant with EIA/TIA, CEI-IEC and ITU standards.

Product Specifications

	Optical Parameters	
Attenuation Max. (dB/km)		
1310 nm		≤ 0.33
1383 nm		≤ 0.31
1550 nm		≤ 0.19
1625 nm		≤ 0.21
Macro bend loss (dB)		
1 turn 7.5 mm radius		≤ 0.2
1 turn 10 mm radius	1550nm	≤ 0.1
10 turns 15 mm radius		≤ 0.03
1 turn 7.5 mm radius	1625nm	≤ 0.5
1 turn 10 mm radius		≤ 0.2
10 turns 15 mm radius		≤ 0.1
Mode Field Diameter (µm) at 1310 nm		9.1 ± 0.4
Mode Field Diameter (µm) at 1550 nm		10.3 ± 0.5
Cable cut-off wavelength (nm)		≤ 1260
Zero dispersion wavelength (nm)		1300 to 1324
Dispersion at 1550nm (ps/nm.km)		≤ 18.6
Zero Dispersion Slope (ps/nm².km)		≤ 0.092
PMD LDV (ps/√ km)		≤ 0.06
Individual Fibre PMD* (ps/√ km) * Individual PMD values may change when cabled		≤ 0.1
Point of discontinuities 1310nm & 1550nm (dB)		≤ 0.05
	Geometrical Parameters	
Cladding Diameter (µm)		125 ± 0.7
Core Clad Concentricity error (µm)		≤ 0.5
Cladding Non-circularity (%)		≤ 0.7
Coating Diameter (uncoloured) (µm)		190 ± 10
Coating Cladding Concentricity error (µm)		≤ 10
Mechani	cal & Environmental Characteristics	
Temperature dependence	-60°C to +85°C	≤ 0.05 (Induced Attenuation at 1310, 1550, 1625 nm (dB/km)
Temperature humidity cycling	-10°C to +85°C, 95% RH	
Water Immersion	30 days, 23 ± 2°C	
High temperature and humidity aging	30 days, 85 ± 2°C, 85% RH	
Accelerated Aging (Temperature)	30 days, 85 ± 2°C	
Proof Testing	,	≥ 125 (kpsi) (0.86GN/m²) (This is equivalent to 1.2% strain)
FibreCurl (m)		≥4
	Performance Characteristics	
Coating strip force		≥ 1.0 N (0.2 lbf) and ≤ 5.0 N (1.1 lbf)
Dynamic fatigue parameter (N)		≥ 20
Effective group index of refraction (Typical Values)		1.4672 at 1310 nm 1.4679 at 1550 nm
Effective group index of refraction (Typical Values)		1.4684 at 1625 nm
Effective group index of refraction (Typical Values) Attenuation in the wavelength region from 1285 - 1330 attenuation at 1310 nm (dB/km)	nm in reference to the	

02/102025

For additional information please contact your sales representative.

You can also visit our website at www.stl.tech